

### PLX160A High Frequency X-Ray System

#### Usage :

This machine is used to photograph patient's chest, stomach, lumbar and extremity.



#### Features :

- 1.It is installed with close-table graphical colorful LCD touch screen, wireless remote control exposure, make the operator easy to use.
- 2.We incorporate the latest compact high-frequency and high-voltage X-ray generator, which ensure superior image quality, while the skin dose is low , to protect the patient better.
- 3.Adopt the technology of kV and mAs numeral Closed loop control , Real-time control of the microprocessor , which ensure the accuracy and repeatability of the output dose.
- 4.Be equipped with radiography parameter of multi-part, multi-posture, multi-body type's adult ,child physical characteristic, the operator can modify and save the parameter by himself, which make the operation more conveniently.
- 5.Possess multiple automatic protection and fault clue function, make the operation more safe and reliable.
- 6.The radiography table can float in any direction, electromagnetic braking, position the patient more convenience and accuracy.
- 7.X-ray generator component can move round the axis of X-ray generator, crossarm and Pillar stand , be convenient with side and slanting direction projection and radiography of patient on the stretcher.
- 8.Be equipped with the bucky stand, which is used in the radiography of the head, chest, belly, pelvic cavity, backbone and periphery.
- 9.Control console of graphic program controlled LCD touch screen is optional, which can set the radiography parameter and exposure in another room.